


Date stamps for foam and deep-drawing molds (Ø10 to Ø12mm)

mirrored, <u>0,5mm</u> raised engraved

Description / Dimension table





- · Complete stamp and input from moulded side changeable
- · Fixing into the mould with M3 thread
- · Engraving mirrored, <u>0,5mm raised</u> (deepened slot in the arrow)
- · Special engravings (e.g. not mirrored) available

material: sleeve/adjustable disc MS58 clamping insert 1.4034, hardened

Mounting



Insert the sleeve and fasten using the clamping insert.

Setting



Release the clamping insert. Make the desired setting on the sleeve and tighten the clamping screw again.

Change



Remove the clamping insert. Take out the sleeve using the lifting thread (M4).

| Туре | Indicator | Order number |
|--------------------|--------------------|--|
| (december 2025) | months + year | KMS10 / 1-12 /(year) KMS12 / 1-12 /(year) |
| (december) | months | KMS10 / 1-12 KMS12 / 1-12 |
| 25 8Z (2025) | 6 years (year + 5) | KMS10 /(year)+5 KMS12 /(year)+5 |
| | | |
| (2025) | year and arrow | EMS10 /(year) EMS12 /(year) |
| | arrow | EMS10 EMS12 |